




- NOTES:
- 1) DRAWING CREATED FROM VENDOR 3D FILE, ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY. VENDOR TO NOTIFY GENERAC OF ANY DESIGN MODIFICATIONS.
  - 2) UL RECOGNIZED COMPONENT, REFERENCE UL FILE AU3493 VOLUME 15, SEC. 2. NO CHANGES TO CONSTRUCTION OR COMPONENTS WITHOUT GENERAC ENGINEERING APPROVAL.
  - 3) ALL FLEXIBLE LEADS TO BE UL RECOGNIZED (AVLU2) MINIMUM RATINGS: 300V, 105° C, 20AWG.
  - 4) VENDOR: CHONGQING LIHUA AUTOMATIC TECHNOLOGY CO LTD PART NUMBER: TT5-4U
  - 5) MAX EXCITATION VOLTAGE: 280VAC  
MAX EXCITATION CURRENT: 30A  
MAX OPERATING TEMP: -20° C TO 85° C **(B)**  
MAX POWER RATING: 7.0 KW.

OK7869  
AS VIEWED FROM  
FRONT OF HOUSING



SCALE 0.333

DRAWING CREATED FROM PRO/ENGINEER 3D FILE. ECO MODIFICATION TO BE APPLIED TO SOLID MODEL ONLY.

2/28/14	-A-	RELEASED FOR PRODUCTION
4/3/14	J-8281B	DM WAS 50, 40 WAS 33 24.7 WAS 22, 95 C WAS 95 C

GENERAL TOLERANCES UNLESS NOTED		THIRD ANGLE PROJECTION	
ALL XX : ± 0.4 MM	XXX : ± 0.4 MM	ALL ANGLES UNLESS NOTED	
ALL ANG : ± 0.5 MM	PER ASME Y14.5M-1998	GENERAL FORM SPECIFIC: THE GEOMETRIC OF THIS DRAWING MUST BE SPECIFIED IN THE FIRST USE OF THE GEOMETRIC OF GENERAL FORM SYSTEMS. IS SUPPLEMENTED WITHOUT THE GEOMETRIC OF GENERAL FORM SYSTEMS.	
DRAWN BY: 1HB	APPROVALS	DATE	3/10/14
ALL APPROVALS ELECTRONICALLY STORED INSIDE WINDCHILL			
LIFE/Cycle STATE: Production Released			
FIRST USE: 0065180			
TITLE		AVR 7KW UL	
MATERIAL		GENERAC MATL SPECIFICATION N/A	
SIZE		CAGE NO DMG NO	
SCALE		0.666 WT-KG 0.00	
SHEET		1 of 1	



OK7869