


GROUP EV



EXPLODED VIEW: EV PPACT POWERHEAD 60HZ

DRAWING #: 0L4787

GROUP

ITEM	PART#	QTY.	DESCRIPTION
1	0C5453	4	SCREW HHTT M8-1.2 X 12 BP
2	0L0208	1	MUFFLER
3	0K6940	1	FLEX PIPE EXH MANI 420CC
4			
5	0K8104	2	CLAMP BAND DIA 31-33mm
6			
7			
8	0J2350B	1	EXHAUST FAN 7KW D-DRIVE
9	0K5974	1	BELLOWS, ALTERNATOR AIR IN
10	0K4216	1	ALTERNATOR DUCT
11	0K5150	1	AIRBOX COVER
12	0K5567	1	BASE AIRBOX INTAKE 420cc
13	0K7336	1	ROTOR BOLT HHC M10 - 1.25 X 335
14	0K9000	6	VIBRATION ISOLATORS
15	10000004854	6	NUT HEX FL WHIZ M10-1.25
16	0H6545	1	GASKET INTAKE 432CC OHV
17	0H6546	1	GASKET INTAKE 432CC OHV
18	0K8835	2	NUT FLANGE M6-1.0 NYLOK
19	0J4298	4	SCREW HHC M6-1.0 X 193 C8.8
20	0K4359	1	ENGINE 420CC GASEOUS
21	0K7282	1	BRUSH ASSEMBLY
22	0K7317	1	SCREW HHFC M5-0.8 X 16
23	0K5614	1	HOSE, BREATHER, 420CC
24	049451	1	WASHER FLAT .406 ID X 1.62 OD
25	046526	1	WASHER LOCK M10
26	0K8391	1	COVER ENGINE BELL
27	0E9371A	1	FILTER AIR GTV530
28	0K5364A	1	ASSEMBLY THROTTLE BODY 420cc
29	0K7869	1	AVR
30	066849	2	SCREW HHTT M5-0.8 X 16
31	0K58490101	1	ROTOR
32	0K58490102	1	STATOR
33	0K58490203	1	BEARING CARRIER
34	0J2004	1	O-RING 50 X 1.5 NITRILE
35	0K9958	1	MANIFOLD
36	0K9065	2	STUD, INTAKE
37	0L3081A	1	JET REGULATOR (LP)
	0L3081B	1	JET REGULATOR (NG)
38	0K5701	1	ANTI-LASH SPRING
39	0K6041	1	LINKAGE
40	045771	2	NUT, HEX M8 - 1.25 G8
41	0L0147	1	HOSE 1/2" ID
42	0F9273	1	SOLENOID
43	077091	1	COTTER PIN
44	0E9592	2	SCREW PPHM #4-40 X 3/8
45	0K9104	3	SCREW HHFC M5 - 0.8 X 10
46	0K5699	1	GOVERNOR SPRING
47	048031M	2	HOSE CLAMP
48	0D1366	1	GOVERNOR ROD BUSHING
49	0K7551	1	HARNESS AVR (NOT SHOWN)
50	029333A	3	TIE WRAP
51	029451	2.7FT	TAPE, FOAM 1/16" X 1/2"