

EXPLODED VIEW: EV ENCLOSURE C2 CPL

DRAWING #: A0000529644

GROUP F

ITEM	PART#	QTY.	DESCRIPTION
1	0K4322	1(REF)	EYE HASP CUST ACCESS BOX
2	0E5968	1	GASKET, EXTRUDED TRIM (327"LG)
3	0H0412	4	NUT U M6-1.0, GEOMET
4	10000004886	1	AL13 PANEL REAR LEFT C2 CPL
	10000004887	1	AL14 PANEL REAR LEFT C2 CPL
	10000004920	1	AL19 PANEL REAR LEFT C2 CPL
5	10000004847	1	AL13 SIDE DOOR RIGHT C2 CPL
	10000004867	1	AL14 SIDE DOOR RIGHT C2 CPL
	10000004910	1	AL19 SIDE DOOR RIGHT C2 CPL
(2) 6	0C2454	14	SCREW HWHT M6-1.0 X 16
(2) 7	0E3257	15	SCREW HWHTF M6-1.0 X 16
8	10000018613	1	CUSTOMER ACCESS ASSSEMBLY
(1) 9	0K40090AL0R	1	FRONT RIGHT CORNER C2
(1) 10	0K40100AL0R	1	FRONT LEFT CORNER C2
11	0K8641	14	SCREW HHFC M6-1.0 X 20 NYL WA
(1) 12	0K37870AL0R	1	PANEL CENTER REAR C2 CPL
(4) 13	G022473	5/6	WASHER FLAT 1/4-M6 ZINC
(1) 14	0K65230AL0R	1	FRONT COVER ENCLOSURE C2
(4) 15	0C2634A	1/2	ASSY ACCESS COVER
16	0K2671	2	INSUL DOOR C2 CPL
17	0F5048D	2	WISE-ACTION LATCH, SLOTTED CIR (36,45 & 60kW UNITS ONLY)
	10000002771	2	LATCH VISE-ACTION 8MM HEX SKT (32, 38 & 48kW UNITS ONLY)
18	0K2671B	2	INSUL CORNER POST C2 CPL
19	0L3103	1	KIT INSULATION C2
19A	0G5892A	1	INSULATION ROOF TOP
19B	0G5892F	1	INSULATION ROOF TOP
20	0F5049B	2	PULL TAB DOOR LOCK ST
21	0F8869D	1	KEY VISE-ACTION LATCH SLOT CIR (36,45 & 60kW UNITS ONLY)
	10000002772	1	LATCH VISE-ACTION 8MM SECURITY KEY (32, 38 & 48kW UNITS ONLY)
22	0K2671E	2	INSUL ROOF SIDES C2 CPL
23	A0000510235	1	AL13 ROOF C2 LOW SPEED (32 & 38KW UNITS ONLY)
	A0000510247	1	AL13 ROOF C2 HIGH SPEED (36, 45 & 60kW UNITS ONLY)
	A0000510237	1	AL19 ROOF C2 LOW SPEED (32 & 38KW UNITS ONLY)
	A0000510252	1	AL19 ROOF C2 HIGH SPEED (36, 45 & 60kW UNITS ONLY)
(4) 24	G022097	5/6	WASHER LOCK M6-1/4
25	10000004848	1	AL13 PANEL REAR RIGHT C2 CPL
	10000004900	1	AL14 PANEL REAR RIGHT C2 CPL
	10000004892	1	AL19 PANEL REAR RIGHT C2 CPL
26	0K2671C	1	INSUL FRONT C2 CPL
27	0J7751	4	SCREW PPHTF #10-16 X 1/2 B
(4) 28	G022127	1/2	NUT HEX 1/4-20 STEEL
29	G080318	4	SCREW HHFC M6-1.0 X 25 FTH G8
30	078115A	12	WASHER SELF LOCKING DOME #8-32
31	G066760	1	STRIP SEALANT 1/8 X 1 (48" LG)
32	0K8973	1	INSULATION
33	0D3059E	2	FOAM, BACK EXHAUST ENCL COVER
(3) 34	0E5298L	1	FOAM 300 X 300 THERMAL ACO
35	0F3890A	4	RETAINER INSULATION (740)
36	0F4051C	1	INSULATION DUCT
37	G077992	26	NUT HEX LOCK M61.0 SS NY INS
38	10000004849	1	AL13 SIDE DOOR LEFT C2 CPL
	10000004891	1	AL14 SIDE DOOR LEFT C2 CPL
	10000004873	1	AL19 SIDE DOOR LEFT C2 CPL
39	10000016218	2	SWITCH ROCKER SPST ON-OFF IP65

NOTES (UNLESS OTHERWISE SPECIFIED):

(1) SHEET METAL PARTS LISTED IN THE BOM TABLE, PRIOR TO 1/11/16, ARE REPRESENTING GENERIC PARTS (NO COLOR) :

- MANUFACTURING: FOR CORRECT MATERIAL AND COLOR REFER TO SAP BOM.
- CUSTOMER: WHEN ORDERING REPLACEMENT PARTS ENTER BASE NUMBER (FIRST 6 DIGITS ONLY) IN THE SYSTEM FOR CORRECT MATERIAL AND COLOR (FOR REFERENCE SEE GUIDELINE 0H7169).

(2) ENCLOSURE NOTE: PANELS THAT FASTEN TO THE BASEFRAME MUST BE SECURED USING I/N 6 & 7 (THREAD FORMING FASTENERS). ALL PANEL TO PANEL CONNECTIONS TO INCLUDE AT LEAST ONE CONNECTION POINT USING I/N 7 (THREAD FORMING FASTENER).

(3) USED ON 48 & 60 KW UNITS ONLY.

(4) QTY. REQ. FOR 32, 38 & 48KW / QTY. REQ. FOR 36, 45 & 60KW.