

Commercial Power Washer

GENERAC® | **PRO**

COMMERCIAL POWER WASHER 4200 psi

Commercial
Power Washer

1 of 2

Model and UPC

G008873-0 – 4200 psi (49-State & Canada) – UPC: 696471079852
G008873-1 – 4200 psi (50-State & Canada) – UPC: 696471079852



*Assembled in the USA using domestic and foreign parts

FEATURES

- **POWER:** The powerful Generac® G-Force OHV engine delivers maximum cleaning performance and reliability. Low-oil shutdown protects the engine.
- **MOBILITY:** Oversized never-flat wheels easily handle rugged jobsite terrain.
- **DURABILITY:** Commercial Grade Direct Drive CAT® Triplex Pumps - Up to 4X longer life than axial cam pumps. The rugged frame is 1.25 in (31.8 mm) welded steel tube with a 12 gauge formed steel baseplate. The 35 ft (10.7 m) steel reinforced hose is durable and non-marring, so it will not leave scuff marks.
- **COMFORT:** The ergonomic spray gun features quick change connections, a stabilizing side handle, a molded grip, and an easy-to-pull trigger for comfort during prolonged use.
- **EASY-TO-USE:** Save time with the easy-to-move 3-wheel design that moves with you around the jobsite to prevent downtime. Features an integrated 5 gal (18.9 L) bucket holder for detergent or onboard storage. Save space with the folding handle for compact storage and transport. The pressure control valve allows for adjustable cleaning power.

4200 psi

GENERAC® | PRO

Specifications

PRESSURE AND FLOW

Maximum outlet pressure (psi / bar)	4,200 / 290
Maximum flow rate (gpm) / (L/min)	4.0 / 15.1

ENGINE

Manufacturer	Generac
Displacement (in ³ / cc)	25.6 / 420
Type	4 cycle / OHV
Orientation	Horizontal
Lubrication method	Splash
Low oil shutdown system	Yes
Fuel capacity (gal / L)	1.6 / 6.5
Fuel ON/OFF valve	Yes
Oil capacity (oz / L)	37 / 1.1
Recommended engine oil	10W-30 / SAE 30
Throttle control	Manual
Choke	Manual
Starting method	Manual / recoil

PUMP

Type	Triplex
Manufacturer	CAT
Plunger	Ceramic
Maximum water supply temperature (°F / °C)	100 / 38
Warranty	5 year limited

HOSE

Type	Polyurethane, steel braided
Length (ft / m)	35 / 10.7
Diameter (in / mm)	0.38 / 9.7
Rating (psi / bar)	4,200 / 290
Connectors	Quick change

DETERGENT SYSTEM

Chemical tank	No
Chemical tank description	5 gal (18.9 L) detergent bucket holder

NOZZELS & DETERGENT

Number of nozzles per unit	5
Nozzle descriptions	0°, 15°, 25°, 40°, Soap

GUN & LANCE

Gun type	Professional
Gun to lance connection	M22 threaded
Gun to hose connection	Quick connect
Lance length (in / cm)	29 / 74
Lance material	Stainless steel
Lance to nozzle connection	Quick connect

FRAME & MISC.

Handle	Folding
Frame construction	1.25 in (31.8 mm) welded steel tube
Wheels (in / mm)	3 x 10 (76.2 x 254) Never Flat

DIMENSIONS & WEIGHTS

Storage unit length (in / cm)	38.1 / 96.8
Extended unit length (in / cm)	51.5 / 130.9
Unit width (wheel to wheel, in / cm)	23.3 / 59.2
Storage unit height (in / cm)	27.6 / 70.1
Extended unit height (in / cm)	32.5 / 82.5
Unit weight (lbs / kg)	151 / 68.5
Boxed length (in / cm)	40.0 / 101.6
Boxed width (in / cm)	27.0 / 68.6
Boxed height (in / cm)	32.8 / 83.3
Boxed weight (lb / kg)	187 / 84.8

WARRANTY

Commercial (unit)	3 year limited
-------------------	----------------