



EXPLODED VIEW: CONTROL PANEL

DRAWING #: 0G7538

APPLICABLE TO: 2008 HSB

ITEM	PART #	QTY.	DESCRIPTION
1	022097	3	WASHER LOCK M6-1/4
2	0G6131	3	SCREW HHC M6-1.0 X 30 C8.8
3	043182	1	WASHER LOCK M3
4	049226	4	WASHER LOCK M5
5	049811	3	WASHER FLAT M6
6	049813	3	NUT HEX M6 X 1.0 G8 YEL CHR
7	051713	4	WASHER FLAT M5 (8kw)
	051713	2	WASHER FLAT M5 (10kw, 14kw, 17kw, & 20kw)
8	052777	1	WASHER FLAT M3
9	066482	4	SCREW HHC M5-0.8 X 10 SEMS
10	082121C	1	CLIP-J VINYL COAT .625 ID (10kw, 14kw, 17kw, & 20kw)
11	0C1069	3	SCREW HHTT M6-1.0 X 8 ZINC (8kw)
	0C1069	2	SCREW HHTT M6-1.0 X 8 ZINC (10kw, 14kw, 17kw, & 20kw)
12	0G9002	2	SCREW PPHM M3-0.5 X 12 SEMS (8kw)
	0G9002	4	SCREW PPHM M3-0.5 X 12 SEMS (10kw, 14kw, 17kw, & 20kw)
13	091526	4	SCREW PPHM M5-0.8 X 12 ZNC
14	0C2174	1	RELAY 12V 25A SPST (10kw, 14kw, 17kw, & 20kw)
15	0E3969	1	SCREW PPHM M3-0.5 X 30
16	0G7820	1	BRKT CTRL PNL BACK 8KW
	0G7652	1	BRKT CTRL PNL BACK 10/14/17/20KW
17	0G7801	1	BASE CONTROL BOX 2008 HSB
18	0G7802	1	DECAL CUSTOMER CONN HSB
19	0G7901	1	ASSY CTRL PNL 2008 AC HSB (8kw)
	0H0643	1	ASSY CTRL PANEL 2008 AC HSB (10kw, 14kw, 17kw, & 20kw)
20	0G7871	1	BLOCK TERM 4POS 15A
21	0D7393R	1	TERM BLOCK 2P UL 12-20AWG
22	0G7837	1	HARNESS, C/PNL 08 S-CYL HSB (NOT SHOWN) (8kw)
	0G7835	1	HARNESS, C/PNL 08 VT HSB (NOT SHOWN) (10, 14, 17, & 20kw)
23	0G7464	1	ASSY CONTROL BOX (17kw, & 20kw)
	0G7464A	1	ASSY CONTROL BOX (10kw, & 14kw)
24	0G7445	1	EYE HASP CNTRL PANEL (10kw, 14kw, 17kw, & 20kw)
25	0G7819	2	PLUG PLASTIC DOME 7/16" (10kw, 14kw, 17kw, & 20kw)
26	0E4261	1	OUTLET, 15A GFCI DUPLEX WHITE (17kw, & 20kw)
27	0G7537	1	CB BRACKET CONTROL BOX (10kw, 14kw, 17kw, & 20kw)
28	0G7621	3	SCREW HH HI-LO M4 X 10MM (17kw, & 20kw)
	0G7621	1	SCREW HH HI-LO M4 X 10MM (10kw, & 14kw)
29	0G7717	2	SCREW REDUCED HH HI-LO M6X10MM (10kw, 14kw, 17kw, & 20kw)
30	0G7714	1	ASSY PCB TRIP LED DISPLAY (17kw, & 20kw)
	0G7714A	1	ASSY, DUAL LED DISPLAY (10kw, & 14kw)
31	045770	2	SCREW HHC M5-0.8 X 10 C8.8 (8kw)
32	082025	2	NUT HEX LOCK M5-0.8 NYINS ZINC (8kw)
33	0E7890	1	BRKT CB MTG BACK (8kw)
34	0G7568	1	CB 0015A 1P 120V S BQ1 LB (17kw, & 20kw)
35	0E7886B	1	CB 0035A 2P 240V S BQ2 LB (8kw)
36	0E7886D	1	CB 0045A 2P 240V S BQ2 LB (10kw)
	0E7886F	1	CB 0060A 2P 240V S BQ2 LB (14kw)
	0E7886J	1	CB 0065A 2P 240V S BQ2 LB (17kw)
	0E7886H	1	CB 0100A 2P 240V S BQ2 LB (20kw)
37	0D7393S	2	CAP LOCKOUT
38	0D7178T	REF	FUSE, ATO TYPE 7.5AMP (BROWN)
39	023484F	1	SNAP BUSHING