


GROUP F



EXPLODED VIEW: EV EXHAUST D2.3L G16**DRAWING #: 0K2287****GROUP F**

ITEM	PART#	QTY.	DESCRIPTION
1	0K3900	2	MUFFLER STRAP
2	022129	4	WASHER LOCK M8-5/16
3	0K2309	1	ASSY EXHAUST TUBE D2.3L G16
4	0K3020G	1	BLANKET EXHAUST 2" 1300MM (NOT SHOWN)
5	036797	2	BOLT/SDL U 5/16-18 X 2.125
6	0K2308	1	EXHAUST ELBOW D2.3L G16
7	022259	4	NUT HEX 5/16-18 STEEL
8	0A8974	1	RAINCAP 2"
9	0K3368	1	MUFFLER 2.4L/3.4L CPL
10	0K1526	2	TIE WRAP, 14.3" STAINLESS STL
11	0E3257	4	SCREW HWHTF M6-1.0 X 16
12	0K3959	1	EXHAUST TUBE STRAIGHT W/ FLARE
13	022473	6	WASHER FLAT 1/4-M6 ZINC
14	0K2310	1	MUFFLER SADDLE M060481
15	0H1310	1	BOLT U 3/8-16 X 2.30 W/SADDLE
16	039287	1	SCREW HHC M8-1.25 X 45 C8.8
17	022145	1	WASHER FLAT 5/16-M8 ZINC
18	052858	1	NUT TOP LOCK FL M8-1.25
(1)19	REF	1	GASKET MANIFOLD
(1)20	REF	1	NUT HEX FLANGE SERRATED M8-1.25
21	042568	1	SCREW HHC M6-1.0 X 20 C8.8
22	0D3701A	1	PLATE "HOT" 50 X 110
23	022097	1	WASHER LOCK M6-1/4
24	049813	1	NUT HEX M6-1.0 G8 CLEAR ZINC

NOTES(UNLESS OTHERWISE SPECIFIED):

(1) INCLUDED WITH ENGINE