


GROUP G

NOTE: ITEMS MARKED BY * ARE PART OF WIRE HARNESS.



MODEL RATING	ITEM L RATING	ITEM L P/N
22KW/27KW 1φ	3A	054502
22KW/27KW 3φ	6A	048505
36KW 1φ/3φ	7A	048467
17.6KW/21.6KW 1φ 50Hz	5A	048512

EXPLODED VIEW:
R-200C 1800 RPM 2.4L
DRAWING #: 0H1433D

APPLICABLE TO:

ITEM	PART #	QTY.	DESCRIPTION
COMPONENTS INCLUDED IN 0H1433E			
1	0F1823B	1	ENCL HSB CONTROL PANEL
2	0F3078BST06	1	COVER CONTROL PANEL R-200B
3	0F2606	1	HINGE CONTINUOUS H-PANEL
4	036261	7	RIVET POP .125 X .275 SS
5	0E7358	4	SCREW PPH HI-LO #4-24 X 3/8
6	052777	1	WASHER FLAT M3
7	0H1176A	1	ASSY PCB R-200C CNTRL 1800 RPM
*8	0F1262	REF.	HOLDER FUSE WICKMANN 178.6150
*9	0F1263	REF.	ADPTR RH SIDE WICKMANN 178.6191
*10	0F1264	REF.	ADPTR LH SIDE WICKMANN 178.6192
11	0G8023A	1	BATC 13.4VDC 2.5A W/4POS PLUG
12	0G2885	1	ASSY PCB HI-PWR VOLTAGE RGLTR
13	0E6875A	2	RELAY 12VDC C FORM W/DIODE
*14	055911	REF.	BLOCK TERM 20A 12 X 6 X 1100V
15	0F5459	1	DECAL CPL CNT PNL FUSES
16	0E3161	1	ASSY PCB BOSCH GOV DRMR
17	0G3648	1	M5X0.8 CAPTIVE PANEL KNLD HD
18	0F5462	1	DECAL CPL 3.9L TB1
19	0A5062J	4	SPACER 9.5H 3.2 ID
20	029673	1	DIO BRIDGE 25A 600V
21	0C1457A	1	HOUR METER 10-80VDC
22	0F1958	1	PLATE HARNESS CLAMP
23	082573	1	SWITCH RKR DPST 125V SPD
24	0E4494	1	SWITCH RKR DPDT ON-OFF-ON
25	0G8997	1	DECAL CONTROL FLEX R-200B
26	0F6305	2	SEAL COVER 3.18X12.7X382
27	0F6305A	1	SEAL COVER 3.18X12.7X283
28	0F5886	2	SCREW HHPM M5-0.8 X 12
29	051713	11	WASHER FLAT M5
30	049226	11	WASHER LOCK M5
31	0F5752F	1	RES WW 15R 5% 25W QK CONN
32	0F5884	2	SCREW PHTT M3.5-0.6 X 10
33	0F5896	2	SCREW PHTT M3.5-0.6 X 16
34	074076	2	SCREW PHM M3-0.5 X 10 BLACK
35	0C3990	2	SCREW PHTT M4-0.7 X 10 ZYC
36	080823	4	SCREW PPHM M5-0.8 X 50 ZNC
37	051716	9	NUT HEX M5-0.8 G8 YEL CHR
38	079224	2	SCREW PPHM M5-0.8 X 30 SS
39	043182	7	WASHER LOCK M3
40	051714	7	NUT HEX M3-0.5 G8 YEL CHR
41	0F3192	1	SUPPORT ANGLE PCB
42	0E7403C	1	FUSE ATO TYPE 15 AMP (BLUE)
43	0G9056	1	HARN CTRL PNL R-200B 2.4L/4.2L (NOT SHOWN)
COMPONENTS INSTALLED PER THIS DRAWING			
A	056739	1	RELAY SOLENOID 12VDC PNL MNT
B	022287	2	SCREW HHC 1/4-20 X 3/4 G5
C	022473	4	WASHER FLAT 1/4-M6 ZINC
D	022097	2	WASHER LOCK M6-1/4
E	022127	2	NUT HEX 1/4-20 STEEL
F	0F6145	A/R	SEAL WEATHER .45"DIA
G	0F2627A	1	COVER CONTROL PANEL SIDE
H	091526	4	SCREW PPHM M5-0.8 X 12 ZNC
J	049226	4	WASHER LOCK M5
K	051713	4	WASHER FLAT M5
L	SEE CHART	1	DPE BREAKER
M	052777	2	WASHER FLAT M3
N	043182	2	WASHER LOCK M3
P	051714	2	NUT HEX M3-0.5 G8 YEL CHR

NOTE: ITEMS MARKED BY * ARE PART OF WIRE HARNESS.